

## **Pocket Sampler**

## Discrete Multilevel Sampler

The highly popular Pocket Sampler is suitable for taking discrete samples from free flowing powders and granules. The sampler is available in a range of sizes and designs.

Type: Multilevel (discrete/zone samples)


Material: 316 Stainless steel outer with a PTFE core or all 316


stainless steel construction

Operation: 1. Insert the sampler into the product

At the required depth rotate handle to expose the collecting pockets, the product will flow into the collecting pockets

Rotate handle to close pockets and remove sampler.





- A Removable Tip allows thorough cleaning
- B Sampling Pockets
- (C) Handle
- (D) Cleaning Brush
- E Outer Tube
- F Inner Rod



Emptying Rack allows samples to be deposited directly into collecting bottles









Part No.	Outer Tube	Inner Rod	No. of Pockets	Volume of Pockets	Sampler Length
1220A-600	316ss	PTFE	3	15ml	600mm
1220A-900	316ss	PTFE	3	20ml	900mm
1220A-1500	316ss	PTFE	5	20ml	1500mm
1220B-600	316ss	316ss	3	15ml	600mm
1220B-900	316ss	316ss	3	20ml	900mm
1220B-1500	316ss	316ss	5	20ml	1500mm
Ancillaries	8005A-01		Sealing Sleeve Set - Covers pockets - set of 3 sleeves		
	1220X-600	1220X-600 Emptying rack for 600mm sampler - stainless steel			
	1220X-900	1220X-900 Emptying rack for 900mm sampler - stainless steel			
	1220X-1500		Emptying rack for 1500mm sampler - stainless steel		
	LUG-1		Earthing connection point.		
	Tip2		Round tip. (Sampler supplied with pointed tip). Use rounded tips when		
			sampling from delicate sacks		
	Cleaning brushes		Download Range Brochure for full details		
	Storage Cases		Download Range Brochure for for	ull details	