

Power Sampler

The Power Sampler consists of a convenient hand held power unit which drives an auger. The auger is used to draw the product up the lance and into the collecting vessel.

Suitability: Free Flowing Powders and granules

Cohesive Powders

Single Point Type:

Material: 316 stainless steel (contact parts). Satin

General: Suitable for taking large volume samples.

Operation: Insert the lance into the product. The auger within

the lance will draw the product up the lance and deposit it in the collecting vessel. Reversing the direction of the auger will allow material within the

lance to be returned at the end of sampling.



Sampling Lances

Two styles of sampling lance are available:



Vertical

Suitable for sampling from the top of containers



Horizontal

Suitable for sampling horizontally. Particularly useful if sampling from



	Part No.	Description		
Drive Unit Sets	Lance supplied with Drive Unit and 2 batteries, Battery Charger (requires 230v 50Hz supply) and Carrying Case			
	Part No.	Length	Suitable for Powders	Lance Type
Lances	1215A-300 1215A-600	300mm 600mm	Up to 2mm in diameter Up to 2mm in diameter	Horizontal Vertical
	1215A-900 1215A-1200	900mm 1200mm	Up to 2mm in diameter Up to 2mm in diameter	Vertical Vertical
	1215B-300	300mm	2mm to 4mm in diameter 2mm to 4mm in diameter	Horizontal
	1215B-600 1215B-900 1215B-1200	600mm 900mm 1200mm	2mm to 4mm in diameter 2mm to 4mm in diameter 2mm to 4mm in diameter	Vertical Vertical Vertical
Accessories	1215W-500		uitable for use in bottle holder)	vertical
	1215C-01	Stainless Steel Bottle Holder - use in place of sterile bags Cleaning Brush - length 1100mm Cleaning Brush - length 1600mm		
	8001A-1100 8001A-1600			

Tel: +44 (0)1675 466992

Fax: +44 (0)1675 466994