


Sack Master

Large Range of High Quality Sack Samplers

The Sack Master has been specially designed to take samples through the side of a sack. A range of sample collection methods are available.


- Type: Single point
- Material: 316 stainless steel
- Operation:
1. Insert the sampler through the side of the sack.
 2. Angle sampler downwards to allow the product to flow into the sample collecting container
 3. Seal the hole using an Ultra Adhesive Label



End Fittings:

Ⓐ Plain

- Sample collecting bag is held over end of sampler
- Plain end
- Electropolished



Ⓑ End Cap

- Cap screws on to end of Sack Sampler
- Easily removed for cleaning
- Sample is retained in Sack Sampler
- Electropolished



Ⓒ Bottle Adapter

- Adapter screws on to end of Sack Sampler
- Sample is collected in either a 250ml or 500ml bottle
- After sampling unscrew bottle and screw on the plastic bottle cap
- Electropolished



Part No.	Sampler Description	Sampler End Fitting
1320A-01	Sack Master P	Plain
1320B-01	Sack Master EC	End Cap
1320C-01	Sack Master BA	Bottle Adapter*
* Sampler supplied with one 250ml Sample Bottle (Part No. 8165A-250)		
Accessories		
8165A-250	Sampling Bottle - 250ml - HDPE - for use with bottle adapter	
8165A-500	Sampling Bottle - 500ml - HDPE - for use with bottle adapter	
8001A-500	Cleaning Brush - 500mm length	
Storage Cases	Please download brochure for further information	